

Orbital Shaker, neoLab®

- Optimal rotation amplitude for intensive mixing
- With digital timer 1 to 999 min.
- Suitable for continuous operation
- Precision speed control
- Rotation: orbital
- Ambient temp. +4°C to +55°C
- Rel. air humidity (20°C): max. 80%
- Acoustic signal after timer has run out
- Supplied with 2 magnetic clips

Connection: 12 V AC adapter, 1000 mA

Platform	Amplitude	L × W × H	Speed	Load capacity max.	Order No.
mm	mm	mm	rpm	kg	
168 × 168	20	193 × 170 × 70	10 – 250	1.5	52 01 70030



WW2NY395

